



GAR1828CG3

by Burndy
Catalog ID: GAR1828CG3

Prop 65 Notice

To Rod or Pipe with the Same Connector.

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	260
UPC	621945138254
UPC 12 Digit	6219451382544

Dimensions

Dimension - B Length inch	1.12 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.12 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

Conductor Related

Conductor - Copper Solid Size	4/0
Conductor - Copper Solid Size Range	4/0
Conductor - Copper Str Size	2/0;3/0;4/0
Conductor - Copper Str Size Range	2/0-4/0
Conductor - Copper Tube Std Size	2
Conductor - Copper Tube Std Size Range	2
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)