

DRAWING NO.
10097423

4

3

2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	05/08/2017 11:56:00 AM	LOGO UPDATE	46694	SV	MB

D

D

C


C

B

B

A

A



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 700 INDOOR, 540 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- 'UL' SYMBOL FOR INTERNAL SPECIFICATION L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

REV: PE0200

4

3

2

1

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES:		ITEM NO: 3320JC	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: B2G14D5	
CANADA:		DRAWN BY: R. BOISVERT 02/26/09	
1-800-361-6975 (QUEBEC)		CHECKER: J. PARKER 02/26/09	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APPVL: J. PARKER 02/13/09	
FOR PRODUCT INFO: http://www.burndy.com		MFG APPVL: -- --	
		QA APPVL: J. BRODEUR 02/25/09	
		MKT APPVL: P. THERRIEN 02/13/09	
		SCALE: 3:4	
		PROD FAM: --	
		PROJECT #: --	
		DOCUMENT TYPE: Sales	
		REL LEVEL: Released	
		DRAWING NO	
		10097423	
		REV	
		B	