



GC2929CG18

by Burndy
Catalog ID: GC2929CG18

Prop 65 Notice

Wire: 2/0- 250 kcmil Cu Direct Burial

Product Details

General

Installation Torque Recommended in-lb	40 LBS/in
Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	621945136854
UPC 12 Digit	6219451368544

Dimensions

Dimension - B Length inch	1.61 in
Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.20 in

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG-250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)