



GK1829CG1

by Burndy
Catalog ID: GK1829CG1

Prop 65 Notice

Accom: 2/0 SOL-250 kcmil Cu Cable Torque: 240 IN-LBS Nom

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	Steel - Galvanized
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	621945014237
UPC 12 Digit	6219450142377

Dimensions

Bolt Size	1/2 in
Dimension - B Length inch	1.62 in
Dimension - Height inch	2.81 in
Dimension - Width fraction	5-1/4 in
Dimension - Width inch	5.25 in
Dimension - Width mm	133 mm

Conductor Related

Conductor Size	2/0 AWG Sol - 250 kcmil
----------------	-------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)