



GD1729TN

by Burndy
Catalog ID: GD1729TN

Mechanical Grounding Connector, 2 Cables to Rod or Tube, 2/0 AWG (Sol) -250 kcmil, 1-1/2" Pipe, 1-5/8"-1-7/8" Rod. DURIUM #6 (U-Bolt), Hex Nuts & SPLW

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin Plated
U Bolt Type	268
UPC	781810416785
UPC 12 Digit	7818104167855

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	1.5
Conductor - Copper Str Size Range	2/0-250
Conductor - Copper Tube Std Size	1-5/8;1-3/4;1-7/8
Conductor - Copper Tube Std Size Range	1-5/8-1-7/8

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)