



C22LH2

by Burndy
Catalog ID: C22LH2

Prop 65 Notice

Cast Bronze Clamp, Cable to Water Pipe, 2/0 AWG -10 AWG, 1-1/4" - 2"
Water Pipe, 3/4" hub

Product Details

General

Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Unplated
UPC	781810142189
UPC 12 Digit	7818101421899

Dimensions

Dimension - Height inch	3.19 in
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.50 in
Dimension - Pad Width inch	1.50 in
Dimension - Width inch	1.00 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Str Size Range	10 AWG-2/0 AWG
Conductor - Pipe EMT Size	1 1/4 in;1 1/2 in;2 in
Conductor - Pipe EMT Size Range	1 1/4 in-2 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)