


BFB10502TH38E27

by Burndy
Catalog ID: BFB10502TH38E27

Prop 65 Notice

Industry-exclusive Compression Solution for flexible Bus Bar Applications

- Industry Exclusive! Only offered by BURNDY®
- Eliminates the need to drill through copper sheets, ensuring a cleaner, faster installation
- Full inspectability with the BURNDY® Engineered System
- 1-hole and 2-hole options available to accommodate spacing requirements
- Most flexible bus bar sizes accommodated
- Locator lines on terminals provide for accurate and consistent crimping
- UL Recognized to UL67 for Panelboard Equipment



Product Details

General

Application	Typically used in panelboards, switchboards, transformers, control panels, and similar applications
Material	Copper
Number of Holes	2
UPC	621945475502

Dimensions

Dimension - Stud Size inch	3/8 in
Height	1.58 in
Length	2.75 in

Certifications and Compliance

Certification - ETL	No
---------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)