

DRAWING NO.
50019360

4

3


2

1

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	02/14/2013 00:00:00 AM	CREATE SALES DRAWING FOR BB024L12D50G18	30504	DD	MB


D

D




C

C



B

B



A

A

NOTES:

- APPROXIMATE AMP. RATING: 93A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

REV: PE0200

4

3

2

1

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		BRAID, FLEXIBLE	
		ITEM NO: 50019218	
		CAT. NO: BB024L12D50G18	
		DRAWN BY: D DHEENA 02/14/2013	
		CHECKER: T REYNOLDS 02/15/2013	
		DSN APPVL: R CRUZ 02/16/2013	
		MFG APPVL: L LEAVITT 02/15/2013	
		QA APPVL: T WATTS 02/15/2013	
		MKT APPVL: K ROBICHEAU 02/15/2013	
		SCALE: 1:1	
		PROD FAM: CM&R COMPRESSION	DRAWING NO
		PROJECT #: --	50019360
		DOCUMENT TYPE: Sales	REV
		REL LEVEL: Released	A

BURNDY