

# YC25A25

by Burndy  
Catalog ID: YC25A25

Prop 65 Notice

Range-taking, C-shaped AL compression tap, Run: Aluminum: 1/0- 2/0, ACSR: 1/0, Tap: Aluminum: 1/0- 2/0, ACSR: 1/0



## Product Details

### General

Die Index	Q
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810123621
UPC 12 Digit	7818101236211

### Dimensions

Dimension - Height inch	1.36 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in

### Conductor Related

Conductor - ACSR Str Run	1/0 Str
Conductor - ACSR Str Tap	1/0 Str
Conductor - AL Str Run	1/0 AWG;2/0 AWG
Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap	1/0 AWG;2/0 AWG
Conductor - AL Str Tap Range	1/0 AWG - 2/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)