



DRAWING NO.
10007413

CATALOG NUMBER	"C"	"D"	"L"	"T"	EATON PART NO.	FIG. NO.	CROSS SECTION AREA (CM)	NOMINAL AMPACITY
B4D10G51TN	1.19 [30]	.60 [15]	10.00 [254]	.32 [8]	6353C90H06	2	308,736	600
B4D25G51TN	1.19 [30]	.60 [15]	25.00 [635]	.32 [8]	--		308,736	600
B4F8G56TN	1.50 [38]	.75 [19]	8.00 [203]	.78 [20]	--		926,208	900
B4F10G56TN	1.50 [38]	.75 [19]	10.00 [254]	.78 [20]	6353C85H02		926,208	900
B4F12G56TN	1.50 [38]	.75 [19]	12.00 [305]	.78 [20]	6353C85H03	1	926,208	900
B2E9G107TN	1.50 [38]	.75 [19]	9.00 [229]	.30 [8]	13B4105H07		307,400	530
B2E15G107TN	1.50 [38]	.75 [19]	15.00 [381]	.30 [8]	13B4105H03		307,400	530

REV.	DATE	DESCRIPTION	ECO	BY	C*K'D.
H	12/5/14	FOCUS NO. #1412013	38600	AS	MB



NOTES:

- "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- BRAID IS FLAT, THERE IS NO .50 BEND.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO: --	
CAT NO: B-- (SEE TABLE)	
SCALE: NTS	
DRAWN BY: P. LAPONUS 05/28/02	
CHECKER: R. BOISVERT 05/31/04	
DSN APPVL: J. MICHAUD 05/10/02	
MFG APPVL: --	
QC APPVL: C. ACKERMAN 05/30/02	
MKT APPVL: D. HAMILTON 05/30/02	
PROJECT #:	SIZE
DOCUMENT TYPE: Sales	D
REL LEVEL: RELEASED	
DRAWING NO	REV
10007413	H
SHEET 1 of 1	