


PIPE SIZES ACCOMMODATED		CONDUCTOR ACCOMMODATED										CATALOG NUMBER	J		L		V		W		H		FRONT "U" BOLT	REAR "U" BOLT	TORQUE	
NOMINAL DIAMETER (IN)	ACTUAL DIAMETER (IN) [MM]	AWG				METRIC WIRE SIZE							(IN)	[MM]	(IN)	[MM]	(IN)	[MM]	(IN)	[MM]	(IN)	[MM]			LB*IN	N*M
		SIZE	DIA.	SIZE	DIA.	SIZE	DIA.	SIZE	DIA.	SIZE	DIA.															
6" MAX	6.625 [168.3]	4 STR	.232	2/0 STR	.416	25mm ² STR	[6.5]	50mm ² STR	[9.27]	GQ2626	1/2	[13]	5	[127]	3	[76]	2.44	[62]	3.72	[95]	400	291	480	54.1		
6" OR GREATER	6.625 [168.3]	4 STR	.232	2/0 STR	.416	25mm ² STR	[6.5]	50mm ² STR	[9.27]	GQ26-1	1/2	[13]	5	[127]	3	[76]	2.44	[62]	6.41	[163]	399	291	480	54.1		
6" MAX	6.625 [168.3]	2/0 STR	.416	250 kcmil	.575	70mm ² STR	[10.9]	120mm ² STR	[14.4]	GQ2929	1/2	[13]	6	[152]	4	[102]	2.75	[70]	3.44	[87]	247	291	480	54.1		
6" OR GREATER	6.625 [168.3]	2/0 STR	.416	250 kcmil	.575	70mm ² STR	[10.9]	120mm ² STR	[14.4]	GQ29-1	1/2	[13]	6	[152]	4	[102]	2.75	[70]	6.81	[173]	392	291	480	54.1		
6" MAX	6.625 [168.3]	300 kcmil	.630	500 kcmil	.814	185mm ² STR	[17.8]	240mm ² STR	[20.3]	GQ3434	1/2	[13]	6.75	[172]	4.5	[114]	2.75	[70]	2.19	[56]	360	254	480	54.1		
6" OR GREATER	6.625 [168.3]	300 kcmil	.630	500 kcmil	.814	185mm ² STR	[17.8]	240mm ² STR	[20.3]	GQ34-1	1/2	[13]	6.75	[172]	4.5	[114]	2.75	[70]	8.31	[211]	398	254	480	54.1		

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	02/01/2022	REDRAWN IN INVENTOR	220125016372	PB	RG



NOTES:

1. MATERIAL: CAST COPPER ALLOY
2. UL 467 LISTED, FILE NO. E9999. ACCEPTABLE FOR DIRECT BURIAL.
3. DIMENSIONS IN BRACKET [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		GROUND CLAMP	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: --	
CANADA: 1-800-387-6487		CAT. NO: GQ- (SEE TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R.PERREAU 7/16/1994	
		CHECKER: KFM 7/26/1994	
		DSN APRVL: G.DITROIA 11/11/1993	
		MFG APRVL: --	
		QA APRVL: A.LLOYD 12/3/1994	
		MKT APRVL: K.WOOD 11/11/1993	
		PROD FAM: --	
		DRAWING NO	
		SD014710-01	
		REV	
		A	
		SHEET 1 OF 1	

