



GD1829CG1

by Burndy
Catalog ID: GD1829CG1

Prop 65 Notice

Accom: 2 IPS Aluminium Pipe - 250 kcmil to 2/0 SOL Cast Copper Alloy

Product Details

General

Material	Copper Alloy, Cast
Material Type - Screw	Steel - Galvanized
Plated	N
Plating Type	Brite Dip
UPC	621945157439
UPC 12 Digit	6219451574399

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Height inch	5 in
Dimension - Width fraction	4 in
Dimension - Width inch	4 in
Dimension - Width mm	102 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	2
Conductor - Copper Str Size Range	2/0-250

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)