



GC34CG2

by Burndy
Catalog ID: GC34CG2

Prop 65 Notice

Ground Connector, CU CABLE: 300 KCMIL - #8 AWG TORQUE: 360 LB
IN Tin Hot Plated

Product Details

General

Installation Torque Recommended in-lb	360 lb-in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Oval Shank Bolt
Plated	N
Plating Type	Tin - Hot Plated
UPC	621945225152
UPC 12 Digit	6219452251522

Dimensions

Dimension - Height inch	2.50 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Pad Width inch	1.44 in
Dimension - Width fraction	2-4/5 in
Dimension - Width inch	2.81 in
Dimension - Width mm	71 mm

Conductor Related

Conductor - Copper Solid Size Range	300 KCMIL - #8 AWG
Conductor - Copper Str Size A	8 AWG;7 AWG
Conductor - Copper Str Size A Range	8 AWG-7 AWG
Conductor - Copper Str Size B	8 AWG;7 AWG
Conductor - Copper Str Size B Range	8 AWG-7 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)