



GC3939

by Burndy
Catalog ID: GC3939

Prop 65 Notice

Mechanical Grounding Connector, 2 Copper Cables to 1/4" Thick Bar, 550 kcmil - 750 kcmil, 5/8" Stud

Product Details

General

Installation Torque Recommended in-lb	660 lb-in
Material	Copper
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810001660
UPC 12 Digit	7818100016600

Dimensions

Dimension - B Length inch	3.63 in
Dimension - D inch	3.31 in
Dimension - F Width Center to Center inch	1.56 in
Dimension - Height inch	3.31 in
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.25 in
Dimension - Length Side A inch	2.25 in
Dimension - Length Side B inch	3.06 in
Dimension - Pad Width inch	1.75 in
Height	3.31 in
Length	2.25 in
Width	3.63 in

Conductor Related

Conductor - Copper Solid Size Range	550 KCMIL - 750 KCMIL
Conductor - Copper Str Size	550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	550 kcmil-750 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)