


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	03/09/2012	CREATE SALES DRAWING	26985	TS	MA



NOTES:

1. APPROXIMATE AMP RATING: 380A INDOOR, 455A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
4. ALL SIZES ARE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		BRAID	
		ITEM NO: 30021553	
		CAT. NO: B2D15G84	
		DRAWN BY: E.MARTIN	2/17/2012
		CHECKER: E.MARTIN	3/20/2012
		DSN APRVL: E.MARTIN	3/20/2012
		MFG APRVL:	
		QA APRVL: J.MEDINA	3/20/2012
		MKT APRVL: P.THERRIEN	3/20/2012
PROD FAM:		DRAWING NO	REV
PROJECT #:		SIZE	
DOCUMENT TYPE: SALES		30025868	A
REL LEVEL: Released		B	SHEET 1 OF 1