



# BD10

by Burndy  
Catalog ID: BD10

Flexible Copper Braid 10 inches long

## Product Details

### General

|                                       |               |
|---------------------------------------|---------------|
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 1             |
| Plated                                | Y             |
| Plating Type                          | Tin           |
| UPC                                   | 781810004876  |
| UPC 12 Digit                          | 7818100048766 |

### Dimensions

|                                 |        |
|---------------------------------|--------|
| Dimension - L Length Overall mm | 254 mm |
| Dimension - Length Overall inch | 10 in  |

### Electrical Ratings

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 190 |
| Rating - Outdoor Amperage | 225 |

### Certifications and Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - CSA Approved       | Yes   |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX    |
| UL Listed                          | Yes   |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)