

## GD1629CG1



by Burndy  
Catalog ID: GD1629CG1

Prop 65 Notice

Accom: 11/4 IPS 1 3/8" - 11/4" ROD 2/0 SOL AWG Min 250 kcmil Cu Max

### Product Details

#### General

Installation Torque Recommended in-lb	360 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	Steel - Galvanized
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Tin - Electro Plated
UPC	621945138995
UPC 12 Digit	6219451389955

#### Dimensions

Dimension - B Length inch	1.25 in
Dimension - Height inch	4.12 in
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

#### Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	1.25
Conductor - Copper Str Size Range	2/0-250

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

## Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us****BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)