



GRF4C4

by Burndy
Catalog ID: GRF4C4

1 or 2 ground conductors (#8 - #2); tin plated cast bronze; up to 5/8" square or 5/8" to 3/4" round pedestals. CSA Certified, UL 467 Listed

Product Details

General

Installation Torque Recommended in-lb	100 LBS/in
Material	Copper Alloy, Cast
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round;Square
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810097878
UPC 12 Digit	7818100978788

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.79 in
Dimension - Height inch	3.13 in
Dimension - Width inch	1.40 in
Dimension - Width mm	36 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor - Pipe or Round Tube Size Range	5/8 in - 3/4 in
Conductor - Pipe or Square Tube Size	5/8 in
Conductor Size	#8 AWG - #2 AWG Sol Str
Number Of Conductors	1;2

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)