



GAR1929TN

by Burndy
Catalog ID: GAR1929TN

Prop 65 Notice

Ground Clamp Copper Tin plated 2/0 AWG-250 kcmil Installation Torque
Recommended Run in-lb240 LB in

Product Details

General

Installation Torque Recommended Run in-lb	240 Lb-in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin plated
U Bolt Type	266
UPC	781810117125
UPC 12 Digit	7818101171255

Dimensions

Dimension - B Length inch	3.25 in
Dimension - Height inch	5.00 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	2.88 in
Dimension - Width inch	4.19 in
Dimension - Width mm	106 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	1/0-250
Conductor - Copper Tube Std Size	2 1/2
Conductor - Copper Tube Std Size Range	2 1/2
Conductor - Pipe or Round Tube Size Range	2-1/2 in
Conductor - Rod Size	2.5 in-2.88 in
Conductor - Rod Size Range	2 1/2-2 3/4

Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)