



ES2R6R

by Burndy Catalog ID: ES2R6R

Prop 65 Notice

RUN/COURSE TAP/DERIVATION ACSR:4 S.B. 200% |8 S.B. 200% AL & CU:2 STR.-2 STR|6 SOL/STR-6 SOL/STR COLOR/COULEUR: A-RED, B-BLUE

Product Details

General

Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Туре	Insulated Service Entrance Connectors
UPC	781810420447
UPC 12 Digit	7818104204477

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	100
i illimidili Fack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)