



BD6T14

by Burndy
Catalog ID: BD6T14

Prop 65 Notice

Flexible Copper Braid 6 in Long

Product Details

General

Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	1
UPC	781810552643
UPC 12 Digit	7818105526433

Dimensions

Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in
Dimension - N inch	0.5 in
Dimension - Stud Size inch	1/4

Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)