



## KSU28

by Burndy  
Catalog ID: KSU28

Prop 65 Notice

Copper Split Bolt w/ Spacer, (Cu & Al): 1-4/0 AWG (Run & Tap)

## Product Details

### General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin Plated
Trade Name	SERVIT®
UPC	781810424162
UPC 12 Digit	7818104241622

### Dimensions

Dimension - Length Overall inch	2.46
Width	1.18 in

### Conductor Related

Conductor - Copper Solid Run Range	1 AWG - 4/0 AWG
Conductor - Copper Solid Tap Range	1 AWG - 4/0 AWG
Conductor - Copper Str Run Range	1 STR - 4/0 STR
Conductor - Copper Str Tap Range	1 STR - 4/0 STR
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Run</li> <li>• AAAC C 5005-Run</li> <li>• AAAC C 6201-Run</li> <li>• ACSR C Str-Run</li> <li>• CU C Solid-Tap</li> <li>• CU C Str-Tap</li> <li>• AL C Str-Tap</li> <li>• AAAC C 5005-Tap</li> <li>• AAAC C 6201-Tap</li> <li>• ACSR C Str-Tap</li> <li>• GAL Steel C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)