



B4D10G51TN

by Burndy
Catalog ID: B4D10G51TN

Prop 65 Notice

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810088326

Dimensions

Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	10.00 in

Electrical Ratings

Amperage Rating	600 A
Rating - Outdoor Amperage	600

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)