



C4LH1

by Burndy
Catalog ID: C4LH1

Prop 65 Notice

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG -6 AWG, 2-1/2" - 4"
Water Pipe, 1/2" hub

Product Details

General

Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Unplated
UPC	781810142219
UPC 12 Digit	7818101422199

Dimensions

Dimension - Height inch	4.56 in
Dimension - L Length Overall mm	122 mm
Dimension - Length Overall inch	4.82 in
Dimension - Pad Width inch	2.44 in
Dimension - Width inch	0.69 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG
Conductor - Copper Solid Size Range	10 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	10 AWG-6 AWG
Conductor - Pipe EMT Size	2 1/2 in;3 in;3 1/2 in;4 in
Conductor - Pipe EMT Size Range	2 1/2 in-4 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	30
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)