



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	06/24/2013	DRAWING RELEASED	32214	DK	MA



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 530 INDOOR, 635 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

3 LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		BRAID	
		ITEM NO: 50026913	
		CAT. NO: B2E27D95G134	
		DRAWN BY: PRASAD, G	06/14/2013
		CHECKER: T. REYNOLDS	06/25/2013
		DSN APRVL: R. CRUZ	06/27/2013
		MFG APRVL: --	
		QA APRVL: J. MEDINA	07/01/2013
		MKT APRVL: K. ROBICHEAU	06/27/2013
		PROD FAM:	
		PROJECT #:	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		SIZE	
		B	
		DRAWING NO	
		50026914	
		SHEET 1 OF 1	
		REV	
		A	