

K14P4CG1

by Burndy
Catalog ID: K14P4CG1

Prop 65 Notice

#14 - #4 AWG Line; #6 - #14 AWG Circuit; 14 Outlets



Product Details

General

Connector Type	Neutral Bar
Material	Copper
Material - Bolt	Steel Zinc Plated
UPC	781810125328

Dimensions

Dimension - Height inch	.48 in
Dimension - Hole Size mm	12 mm
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.74 in
Dimension - Width inch	0.35 in
Dimension - Width mm	9 mm

Conductor Related

Conductor Range	#4 AWG to #14 AWG
-----------------	-------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Carton Quantity	144 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)