


CATALOG NO. 3	ITEM NUMBER	L
BD7G163	332541	7.00 in
BD12G163	332546	12.00 in
BD18G163TN	10094120	18.00 in
BD24G163TN	25019765	24.00 in
BD36G163TN	25019766	36.00 in.
BD38G163	332547	38.00 in
BD72G163TN	25019767	72.00 in
BD76G163TN	25019769	76.00 in
BD78G163TN	25019768	78.00 in
BD120G163TN	25019770	120.00 in
BD144G163TN	25019771	144.00 in

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	08/11/2011 04:00:00 AM	CREATION OF SALES DRAWING	25309	BD	MA



NOTES:

- APPROXIMATE AMP RATING: INDOOR: 190A, OUTDOOR: 225A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY.
- SUFFIX "TN" DENOTES TIN PLATING.
- ALL SIZES ARE LISTED TO UL 467 GROUNDING AND BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING AND BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES:		ITEM NO: (SEE TABLE)	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BDG163 (SEE TABLE)	
CANADA:		DRAWN BY: B.DURAICHAMY 08/11/11	
1-800-361-6975 (QUEBEC)		CHECKER: E.MARTIN 08/09/11	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APPVL: E.MARTIN 08/09/11	
FOR PRODUCT INFO: http://www.burndy.com		MFG APPVL: O.GUALBERTO 08/29/11	
		QA APPVL: C.ACKERMAN 08/09/11	
		MKT APPVL: P.THERRIEN 08/09/11	
		SCALE: 1:1	
		DRAWING NO	
		REV	
		PROJECT #: --	
		SIZE	
		DOCUMENT TYPE: Sales	
		B	
		30018574	
		SHEET 1 OF 1	
		A	