



## GP1726

by Burndy  
Catalog ID: GP1726

Prop 65 Notice

GROUND CONNECTOR RUN: IPS: 1 1/2" ROD: 1 5/8" - 1 7/8" COPPER  
CABLE: 4 SOL. - 2/0 STR.

## Product Details

### General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	268
UPC	781810079218
UPC 12 Digit	7818100792188

### Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	2.31 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

### Conductor Related

Conductor - Rod Size Range	1 5/8" - 1 7/8"
Conductor Size	#4 Sol AWG - 2/0 Str AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)