

DRAWING NO.  
10017511


4

3

2

1

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	12/10/07	ADDED FLAG & TEXT NOTE #3	15258	PL	DB



NOTES:

1. APPROXIMATE AMP RATING: INDOOR = 600, OUTDOOR = 720. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3 "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY®PRODUCTS CALL 1-800-346-4175  
MANCHESTER, NH 03109, USA  
FOR PRODUCT INFO = <http://www.fciconnect.com>

BRAID

ITEM NO: 3321AD

CAT NO: B4D14

SCALE: 1/1  
DRAWN BY: P LAPONIUS 11/5/02  
CHECKER: D BOISVERT 11/5/02  
DSN APPVL: J MICHAUD 10/15/02  
MFG APPVL: ---  
QC APPVL: J BRODEUR 10/17/02  
MKT APPVL: D HAMILTON 10/15/02  
PROD FAM: ---  
PROJECT #: ---  
DOCUMENT TYPE: Sales  
REL LEVEL: AutoCAD

**BURNDY**  
PRODUCTS

DRAWING NO	REV
10017511	B
SHEET 1 OF 1	