



GAR8634

by Burndy
Catalog ID: GAR8634

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 300 kcmil - 500 kcmil, 6" Pipe, Bright Dipped

Product Details

General

Installation Torque Recommended in-lb	480 lb-in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
UPC	781810215814
UPC 12 Digit	7818102158144

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Height fraction	8-13/16 in
Dimension - Height inch	8.75 in
Dimension - L Length Overall mm	52 mm
Dimension - Length BB inch	2.06 in
Dimension - Length Overall inch	2.06 in
Dimension - Outside Diameter inch	6.63 in
Dimension - Width fraction	8-3/8 in
Dimension - Width inch	8.38 in
Dimension - Width mm	213 mm

Conductor Related

Conductor - Copper Solid Size Range	300 kcmil - 500 kcmil
Conductor - Copper Str Size	300;350;400;450;500
Conductor - Copper Str Size Range	300-500
Conductor - Copper Tube Std Size	6
Conductor - Copper Tube Std Size Range	6
Conductor - Pipe or Round Tube Size	6 in
Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)