



GP174C

by Burndy
Catalog ID: GP174C

Prop 65 Notice

Mechanical grounding connector, 1 1/2" Pipe Size, 1 5/8" - 1 7/8" Rod Size,
8 SOL - 4 STR Wire Size, 660 LBS/in Installation Torque.

Product Details

General

Installation Torque Recommended in-lb	660 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	268
UPC	781810426869

Dimensions

Bolt Size	5/8 in
Dimension - B Length inch	2.31 in
Dimension - L Length Overall mm	33 mm
Dimension - Length Overall inch	1.31 in
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Rod Size Range	1 5/8" - 1 7/8"
Conductor Size	#8 AWG SOL - 4 AWG STR

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	14
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)