



GD1629CG1TN

by Burndy

Catalog ID: GD1629CG1TN

Prop 65 Notice

Accom: IPS; 1-1/4 Cu Rod: 1 3/8" or 1-1/4" ; 2/0 SOL Min- 250 kcmil Max Cu

Product Details

General

Installation Torque Recommended in-lb	360 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	Steel - Galvanized
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
Plating Type	Tin Plated
UPC	621945200807
UPC 12 Digit	6219452008077

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Height inch	4.12 in
Dimension - Width fraction	3-1/4 in
Dimension - Width inch	3.25 in
Dimension - Width mm	83 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	1.25
Conductor - Copper Str Size Range	2/0-250

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)