



B2E15G107TN

by Burndy
Catalog ID: B2E15G107TN

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810088388
UPC 12 Digit	7818100883888

Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	381 mm
Dimension - Length Overall inch	15.00 in
Dimension - N inch	0.75
Dimension - Pad Width inch	1.5

Electrical Ratings

Rating - Outdoor Amperage	530
---------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)