



B5G16CG2

by Burndy
Catalog ID: B5G16CG2

Prop 65 Notice

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	5
Plated	Y
UPC	781810460603
UPC 12 Digit	7818104606033

Dimensions

Dimension - L Length Overall mm	419 mm
Dimension - Length Overall inch	16.50 in

Electrical Ratings

Rating - Outdoor Amperage	1500
---------------------------	------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)