



# B3F14NSL

by Burndy  
Catalog ID: B3F14NSL

Prop 65 Notice

Flexible Copper Braid

## Product Details

### General

|                                       |               |
|---------------------------------------|---------------|
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 3             |
| Plated                                | Y             |
| UPC                                   | 781810285992  |
| UPC 12 Digit                          | 7818102859922 |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 356 mm   |
| Dimension - Length Overall inch | 14.00 in |

### Electrical Ratings

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 820 |
| Rating - Outdoor Amperage | 980 |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)