




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	05/02/2017 15:47:00 PM	LOGO UPDATION --	46590	BK	MB



ISOMETRIC VIEW

- NOTES:
- DIMENSION IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
 - MATERIAL: BRAID- TINNED COPPER.
FERRULES- TINNED COPPER.
 - APPROXIMATE AMP. RATING: 1000A.
THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID			
ITEM NO: 10099385			
CAT. NO: B32F12G16TN			
DRAWN BY: S PANDIAN	5/4/09		
CHECKER: J PARKER	6/15/09		
DSN APPVL: J PARKER	6/15/09		
MFG APPVL: L LEAVITT	6/3/09		
QA APPVL: J BRODEUR	6/9/09		
MKT APPVL: P THERRIEN	6/3/09	SCALE: 7:8	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: --	SIZE	10101265	
DOCUMENT TYPE: Sales	C	C	
REL LEVEL: Released		SHEET 1 OF 1	