



GP2226

by Burndy
Catalog ID: GP2226

Prop 65 Notice

Mechanical grounding connector, 4 AWG Solid - 2/0 AWG Stranded, 4" Pipe, 4" Rod, 240 LBS/in Installation Torque.

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	261
UPC	781810001653

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	4.50 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	5-13/16 in
Dimension - Width inch	5.81 in
Dimension - Width mm	148 mm

Conductor Related

Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size Range	5-2/0
Conductor - Rod Size	4 in
Conductor Size	#4 Sol AWG - 2/0 Str AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)