





REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	11/20/2012	NEW SALES DRAWING CREATED	29730	BSB	AD



.25
[6]
(2 PLACES)



DETAIL A
SCALE 1 : 1



- NOTES:
1. APPROXIMATE AMP RATING: 380A INDOOR, 455A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
 2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
 - 3 > BRAID LISTED TO UL 467 GROUNDING AND BONDING EQUIPMENT STANDARDS.
 - 4 > BRAID LISTED TO CSA 22.2 NO. 41 GROUNDING AND BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID, FLEXIBLE	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50014972	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: B2D24D60G74TN	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: SURESH BABU 11/20/2012	
		CHECKER: T.REYNOLDS 12/12/2012	
		DSN APRVL: T.REYNOLDS 11/21/2012	
		MFG APRVL: --	
		QA APRVL: J.MEDINA 1/4/2013	
		MKT APRVL: K.ROBICHEAU 12/13/2012	DRAWING NO 50014973 SHEET 1 OF 1
		PROD FAM: MECHANICAL GROUNDING	
		PROJECT #: --	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	REV A