



GXW2C25

by Burndy
Catalog ID: GXW2C25

Prop 65 Notice

Accom: Groove A: #6- #2 Cu Groove B: 1/0 Cu

Product Details

General	
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Trade Name	GROUNDWEJ™
UPC	781810441121
UPC 12 Digit	7818104411211

Dimensions	
Dimension - B Length inch	1.80 in
Dimension - Pad Width inch	2.80 in

Conductor Related	
Conductor - Copper Solid Size A	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size A Range	6 AWG-2 AWG
Conductor - Copper Solid Size B	1/0 AWG
Conductor - Copper Solid Size B Range	6 AWG-2 AWG
Conductor - Copper Str Size A	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size A Range	6 AWG-2 AWG
Conductor - Copper Str Size B	1/0
Conductor - Copper Str Size B Range	1/0
Conductor Type	• CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B • Rod-Size B

Certifications and Compliance	
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)