


DRAWING NO.
10076470

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
C	01/26/10	CHANGE HOLE DIA. FROM .41 TO .44 PER M/U.	20133	RB	JP



NOTES:

- APPROXIMATE AMP RATING: 415 INDOOR, 495 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- ③ INSIDE HOLES, AND FERRULE ENDS ARE ALSO HOT TIN DIPPED FOR END FERRULES ONLY. INSIDE HOLES FOR CENTER FERULE HOLES ARE NOT HOT TIN DIPPED.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	BRAID	
	ITEM NO: 10074224	
	CAT NO: CBG13G6W	
	SCALE: 1/1	
	DRAWN BY: R BOISVERT 2/12/07 CHECKER: P LAPONIUS 2/13/07 DSN APPVL: J MICHAUD 2/7/07 MFG APPVL: L LEAVITT 2/7/07 QC APPVL: J BRODEUR 2/7/07 MKT APPVL: P THEIRREN 2/7/07	
PROD FAM: --- PROJECT #: --- DOCUMENT TYPE: Sales REL LEVEL: AutoCAD	SIZE: C DRAWING NO: 10076470 REV: C SHEET 1 OF 1	