



GP64528G1

by Burndy
Catalog ID: GP64528G1

Prop 65 Notice

3/8" Bolt size; Conductor Run #4 Solid - 4/0 AWG Stranded, 1 or 2 conductor; copper alloy; accepts 3/4-1" round pedestal or 3/4-7/8" square pedestal

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Pedestal Type	Round;Square
Plated	N
Plating Type	Unplated
U Bolt Type	UB222
UPC	781810657508
UPC 12 Digit	7818106575088

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

Conductor Related

Conductor - Copper Str Size Range	4 AWG-4/0 AWG
Conductor Size	#4 AWG Sol - 4/0 AWG Str
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)