

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	05/02/2017 13:39:00 PM	LOGO UPDATE	46639	BK	MB

D

D

C

C

B

B

A

A

NOTES:

1.

APPROXIMATE AMP RATING: 530 INDOOR, 635 OUTDOOR. THIS RATING MAY VERY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

2.

DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO TEH NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.

3.

MATERIAL:
FERRULE: ETP COPPER, TIN PLATED.
BRAID: COPPER, 2X24X32X30, 2 PCS, TIN PLATED.

4

ALL SIZES LISTED TO UL 467 GROUNDING & BOARDING EQUIPMENT ATANDARDS.

TO ORDER BURNDY® PRODUCTS CALL
UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)
CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)
FOR PRODUCT INFO: <http://www.burndy.com>

BRAID, FLEXIBLE

ITEM NO: 27000284

CAT. NO: B2E12CG35

DRAWN BY: R. BOISVERT 09/17/07

CHECKER: P. LAPONIUS 09/18/07

DSN APPVL: J. MICHAUD 09/14/07

MFG APPVL: -- --

QA APPVL: J. BRODEUR 09/13/07

MKT APPVL: -- --

PROD FAM: --

PROJECT #: --

DOCUMENT TYPE: Sales

REL LEVEL: Released

SCALE: 1:1

DRAWING NO

10081400

SHEET 1 OF 1

REV

C

BURNDY

