



GAR2229TN

by Burndy
Catalog ID: GAR2229TN

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol)
-250 kcmil, 4" Pipe, 4"-4-1/2" Rod, Tin Plated.

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Plating Type	Tin - Hot Dipped
U Bolt Type	261
UPC	621945449398

Dimensions

Dimension - B Length inch	4.50 in
Dimension - Height inch	6.38 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	4.50 in
Dimension - Width inch	5.82 in
Dimension - Width mm	148 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0 AWG-250 Kcmil
Conductor - Copper Str Size	1/0;2/0;3/0;4/0;250
Conductor - Copper Str Size Range	1/0-250
Conductor - Copper Tube Std Size	4;4 1/2
Conductor - Copper Tube Std Size Range	4-4 1/2
Conductor - Pipe or Round Tube Size	4 in
Conductor - Rod Size	4.0 - 4.5 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)