



| REV | DATE       | DESCRIPTION                             | ECO   | BY  | C'H'K. |
|-----|------------|---|-------|-----|--------|
| A   | 08/25/2012 | CREATE DRAWINGS FOR CAT.# B3G11D50G67SV | 28628 | MRA | MB     |



- NOTE:
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
  - APPROXIMATE AMP RATING: 960 INDOOR, 1150 OUTDOOR  
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
  - ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
  - SUFFIX 'SV' DENOTES SILVER PLATED FERRULES.

|   |  |                                 |  |
|---|--|---------------------------------|--|
| TO ORDER BURNDY® PRODUCTS CALL  |  | BRAID                           |  |
| UNITED STATES   |  | ITEM NO: 50008274               |  |
| 1-800-346-4175 (LONDONDERRY, NH)  |  | CAT. NO: B3G11D50G67SV          |  |
| CANADA:   |  | DRAWN BY: E.MARTIN 8/23/2012    |  |
| 1-800-361-6975 (QUEBEC)   |  | CHECKER: R.CRUZ 8/30/2012       |  |
| 1-800-387-6487 (ALL OTHER PROVINCES)  |  | DSN APRVL: E.MARTIN 8/30/2012   |  |
| FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a> |  | MFG APRVL: -- 8/30/2012         |  |
|   |  | QA APRVL: J.MEDINA 8/30/2012    |  |
|   |  | MKT APRVL: P.THERRIEN 8/30/2012 |  |
|   |  | PROD FAM: MECHANICAL GROUNDING  |  |
|   |  | PROJECT #: --                   |  |
|   |  | SIZE                            |  |
|   |  | B                               |  |
|   |  | DRAWING NO                      |  |
|   |  | 50008275                        |  |
|   |  | REV                             |  |
|   |  | A                               |  |
|   |  | SHEET 1 OF 1                    |  |