



GK6429W

by Burndy
Catalog ID: GK6429W

Prop 65 Notice

ACCOMMODATES: 3/8" IPS 5/8-3/4" ROD 2/0SOL - 250kcmil CU
ACCEPTABLE FOR DIRECT BURIAL

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
Type	Three Cables to Rod or Tube
U Bolt Type	540
UPC	781810079188
UPC 12 Digit	7818100791888

Dimensions

Dimension - B Length inch	1.63 in
Dimension - Height inch	2.88 in
Dimension - Width fraction	3-1/2 in
Dimension - Width inch	3.50 in
Dimension - Width mm	89 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	1/0;2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	0.375
Conductor - Copper Str Size Range	1/0-250
Conductor - Copper Tube Std Size	5/8;3/4
Conductor - Copper Tube Std Size Range	5/8-3/4

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)