



GAR1428CG1

by Burndy
Catalog ID: GAR1428CG1

Prop 65 Notice

Mechanical Ground Connector

Product Details

General

Installation Torque Recommended in-lb	170
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	249
UPC	621945011946
UPC 12 Digit	6219450119466

Conductor Related

Conductor - Rod Size Range	3/4" IPS to 2/0
----------------------------	-----------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)