

CT120400D

by Burndy
Catalog ID: CT120400D

Nylon UNIRAP - 120 Lb. Tensile Strength

- Standard Cable Tie



Product Details

General

Color	Natural
Material	Nylon 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength lbs	120
Trade Name	UNIRAP™
UPC	781810333273

Dimensions

Dimension - Bundle Diameter Max inch	4
Dimension - L Length Overall mm	383 mm
Dimension - Length Overall inch	15.09 in
Dimension - Width inch	0.3 in
Dimension - Width mm	8 mm

Certifications and Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-3-9
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	2000 EA
Minimum Pack Quantity	1000

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)