


REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	12/10/2015	NEW SALES DRAWING CREATED	42386	RM	RG



- NOTES:
1. APPROXIMATE AMP RATING: 340A INDOOR, 405A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
  2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
  3. ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
  4. ALL SIZES ARE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		FLEXIBLE BRAID	
UNITED STATES		ITEM NO: 10059223	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BE13G154TN	
CANADA:		DRAWN BY: RAJESHKUMAR M 12/10/2015	
1-800-361-6975 (QUEBEC)		CHECKER: R. GLEN 12/10/2015	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: T. LOGAN 12/10/2015	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		MFG APRVL: O. GUALBERTO 12/11/2015	
		QA APRVL: V. EDUARDO 12/11/2015	
		MKT APRVL: R. KATHLEEN 12/11/2015	
PROD FAM: CM&R COMPRESSION		DRAWING NO	REV
PROJECT #: --		50066428	A
DOCUMENT TYPE: SALES		SIZE	
REL LEVEL: Released		B	
		SHEET 1 OF 1	