



GAR6429W

by Burndy
Catalog ID: GAR6429W

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol)
-250 kcmil, 3/8" Pipe, 5/8"-3/4" Rod, #5-#6 Rebar, Tin Hot Dipped.

Product Details

General

Installation Torque Recommended in-lb	240 lb-in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
Plating Type	Tin - Hot Dipped
U Bolt Type	269
UPC	781810103821
UPC 12 Digit	7818101038211

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height inch	2.88 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	0.68 in
Dimension - Width inch	2.06 in
Dimension - Width mm	52 mm

Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	1/0;2/0;3/0;4/0;250
Conductor - Copper Str Size Range	1/0-250
Conductor - Copper Tube Std Size	3/8
Conductor - Copper Tube Std Size Range	3/8
Conductor - Pipe or Round Tube Size	3/8 in
Conductor - Rebar Size	5;6
Conductor - Rebar Size Range	5-6
Conductor - Rod Size	0.625in - 0.75in
Conductor - Rod Size Range	5/8-3/4

Conductor Type	• CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)