



## GCL30P2W

by Burndy  
Catalog ID: GCL30P2W

Prop 65 Notice

#4 SOL. - 300 kcmil COPPER CONDUCTOR

## Product Details

### General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material - Hardware	Copper Alloy
Plated	Y
Plating Type	Tin - Hot Dipped
UPC	781810100974
UPC 12 Digit	7818101009744

### Dimensions

Dimension - Bus Thickness inch	.25 in
Dimension - L Length Overall mm	53 mm
Dimension - Length Overall inch	2.07 in
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

### Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	4 AWG-4/0 AWG
Conductor - Copper Str Size	5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil
Conductor - Copper Str Size Range	5 AWG-300 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)